

MDA

Management Development Apparatus

di Riccardo Blasi

X-Ray Film Viewer **(XRFV/L)**


Elegant and Slim Design

Superior Luminance by LCD TV Technology

High Quality Radiographic Viewer





DIMENSIONS



INSTALLATION OPTIONS



SPECIFICATIONS

MODEL NAME		LD11A	LD12A	LD13A	LD14A
Dimensions (W × H × D _{mm})	Frame	540 × 493 × 39	895 × 493 × 39	1,251 × 493 × 39	1,606 × 493 × 39
	View	356 × 422	711 × 422	1,067 × 422	1,422 × 422
Film Capacity		14" × 17", 1 bank	14" × 17", 2 bank	14" × 17", 3 bank	14" × 17", 4 bank
Luminance		3,500cd/m ² ± 10%			
Light source		EEFL			
Lamp Life-Time		20,000~50,000 hours			
Switch/Optional Dimmer		Rotary on-off switch for each bank with optional dimming (approx. 50~100% range)			
Film Clip Type		Rolling Bar			
Ambient Temperature		Operation 10°C~40°C, Storage -15°C~60°C			
Power Supply	Input	AC 100~240V, 50~60Hz			
Power Consumption		M ax.55W	Max.110W	Max.165W	Max.220W
Net Weight		Approx. 3.3kg	Approx. 5.5kg	Approx. 9.4kg	Approx. 12.1kg
Mounting Type (standard wall mount)		Wall / Stand / Handle		Wall / Stand	
Safety Agency		 		© Patent pending	

Options

- Fuctional Options : 1) FAS (Film Activating Switch) 2) Dimming
- Installation Options : 1) Desk top stand 2) Handle-type